




Photo shows 843 TableTop® Chain with top plates molded in Low Friction (LF) material on Carbon Steel (S) base chain.



Chain Information						
Chain Width		Min. Side-flex Radius		Approximate Weight		
desc	in	mm	in	mm	lbs/ft	kg/m
1 3/8	1.38	34.9	-	-	0.56	0.83
1 7/16	1.44	36.5	-	-	0.56	0.83
2	2.00	50.8	-	-	0.60	0.89
3 1/4	3.25	82.6	-	-	0.69	1.03

Available Materials												
Prefix	Top Plate Material	Base Chain Material	Temperature							Chain Strength		FDA Approval
			Fahrenheit			Celsius				lbs	N	
			min	max	dry	wet	min	dry	wet			
Standard Materials												
D	Plain Acetal	Carbon Steel	-40	180	NR	-40	82	NR	800	3,559	No	
LF	Low Friction	Carbon Steel	-40	180	NR	-40	82	NR	800	3,559	No	
Made-to-Order Materials												
AS	Anti-Static	Carbon Steel	0	180	NR	-18	82	NR	800	3,559	No	
BWR	Black Wear Resistant	Carbon Steel	-40	180	NR	-40	82	NR	800	3,559	No	
MR	Melt Resistant	Carbon Steel	-80	220	NR	-62	104	NR	800	3,559	No	
P	Chemical Resistant	Carbon Steel	0	180	NR	-18	82	NR	800	3,559	No	

### Regulatory Information

The Food and Drug Administration (FDA) accepts certain materials for direct food contact. FDA approved material is compliant to FDA 21 CFR § 177.

Rexnord and TableTop are trademarks of Rexnord Industries, LLC. All rights reserved.

### Additional Notes

Stocked in 240 pitch, 10 ft (3.048 m) length strands.  
 Uses 843 carbon steel (S) base chain (Part #843S-BC).  
 Chain runs on ANSI No. 40 sprockets.  
 Chain breaker available.  
 Chain strength is listed at room temperature. NR = Not Recommended.  
 For additional material information, see material portfolio.

Part #SK12776

