


Photo shows 3873 TAB TableTop® Chain with top plates molded in Plain Acetal (D) material on Carbon Steel (S) base chain.



### Chain Information

Chain Width		Min. Side-flex Radius		Approximate Weight		
desc	in	mm	in	mm	lbs/ft	kg/m
10	10.00	254.0	18.00	457.2	2.10	3.13
12	12.00	304.8	24.00	609.6	2.30	3.43

### Available Materials

Prefix	Top Plate Material	Base Chain Material	Temperature						Chain Strength		FDA Approval
			Fahrenheit			Celsius			lbs	N	
			min	max	dry	wet	min	max			
Standard Materials											
D	Plain Acetal	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
Made-to-Order Materials											
BWR	Black Wear Resistant	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
LF	Low Friction	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
WD	White Plain Acetal	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No

### Regulatory Information

Rexnord and TableTop are trademarks of Rexnord Industries, LLC. All rights reserved.

### Additional Notes

Stocked in 160 pitch, 10 ft (3.048 m) length strands.  
 Uses 63 carbon steel (S) base chain (Part #63-BC).  
 Chain runs on ANSI No. 60 sprockets.  
 Low Friction (LF) material is stocked for the 10 in (254.0 mm) width only; white alloy plastic (W) material is stocked for the 12 in (304.8 mm).  
 Chain breakers available.  
 Chain strength is listed at room temperature.  
 NR = Not Recommended.  
 For additional material information, see material portfolio.





Photo shows 3873 TAB TableTop® Chain with top plates molded in Low Friction (LF) material on Stainless Steel (SS) base chain.

Chain Information						
Chain Width		Min. Side-flex Radius		Approximate Weight		
desc	in	mm	in	mm	lbs/ft	kg/m
10	10.00	254.0	18.00	457.2	2.10	3.13
12	12.00	304.8	24.00	609.6	2.30	3.43



### Available Materials

Prefix	Top Plate Material	Base Chain Material	Temperature						Chain Strength		FDA Approval
			Fahrenheit			Celsius			lbs	N	
			min	max dry	max wet	min	max dry	max wet			
<b>Standard Materials</b>											
D	Plain Acetal	Stainless Steel	-40	180	150	-40	82	66	750	3,336	No
W	White Alloy Plastic	Stainless Steel	0	180	140	-18	82	60	750	3,336	No
<b>Made-to-Order Materials</b>											
BWR	Black Wear Resistant	Stainless Steel	-40	180	NR	-40	82	NR	750	3,336	No
LF	Low Friction	Stainless Steel	-40	180	150	-40	82	66	750	3,336	Yes
P	Chemical Resistant	Stainless Steel	0	180	140	-18	82	60	750	3,336	Yes
WD	White Plain Acetal	Stainless Steel	-40	180	150	-40	82	66	750	3,336	Yes
WLF	White Low Friction	Stainless Steel	-40	180	150	-40	82	66	750	3,336	Yes

#### Regulatory Information

The Food and Drug Administration (FDA) accepts certain materials for direct food contact. FDA approved material is compliant to FDA 21 CFR § 177.

Rexnord and TableTop are trademarks of Rexnord Industries, LLC.  
All rights reserved.

#### Additional Notes

Stocked in 160 pitch, 10 ft (3.048 m) length strands.  
 Uses 63 stainless steel (SS) base chain (Part #63SS-BC).  
 Chain runs on ANSI No. 60 sprockets.


Low Friction (LF) material is stocked for the 10 in (254.0 mm) width only; white alloy plastic (W) material is stocked for the 12 in (304.8 mm).

Chain breakers available.  
 Chain strength is listed at room temperature.  
 NR = Not Recommended.  
 For additional material information, see material portfolio.

Part #CB1  
Part #SK12776




**Corner Track (Two Piece)**



Corner track kit supplied as one 90° inside and one 90° outside track, which can be used as either carry or return.

Corner Track Kit Number	Accommodates Top Plate Width		Nominal Corner Radius		Inside Track Radius		Outside Track Radius		Thickness		Width		Material	Color	Approximate Corner Track Kit Weight	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm			lbs	kg
<b>TAB Design</b>																
U18R6	All	All	18.0	457	17.3	439	18.7	475	0.75	19.1	1.50	38.1	UHMWPE	White	2.63	1.19
U24R6	All	All	24.0	610	23.3	592	24.7	627	0.75	19.1	1.50	38.1	UHMWPE	White	3.51	1.59

**Corner Track (Four Piece)**



Corner track kit supplied as two 45° inside and two 45° outside track, which can be used as either carry or return.

Corner Track Kit Number	Accommodates Top Plate Width		Nominal Corner Radius		Inside Track Radius		Outside Track Radius		Thickness		Width		Material	Color	Approximate Corner Track Kit Weight	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm			lbs	kg
<b>TAB Design</b>																
U30R6	All	All	30.0	762	29.3	744	30.7	780	0.75	19.1	1.50	38.1	UHMWPE	White	4.38	1.99