


Photo shows 863 TAB TableTop® Chain with top plates molded in Low Friction (LF) material on Carbon Steel (S) base chain.



Chain Information						
Chain Width		Min. Side-flex Radius		Approximate Weight		
desc	in	mm	in	mm	lbs/ft	kg/m
3 1/4	3.25	82.6	-	-	1.41	2.10
4 1/2	4.50	114.3	-	-	1.50	2.24

Available Materials												
Prefix	Top Plate Material	Base Chain Material	Temperature							Chain Strength		FDA Approval
			Fahrenheit			Celsius				lbs	N	
			min	max	dry	wet	min	dry	wet			
Standard Materials												
LF	Low Friction	Carbon Steel	-40	180	NR	-40	82	NR	1,400	6,228	No	
Made-to-Order Materials												
BWR	Black Wear Resistant	Carbon Steel	-40	180	NR	-40	82	NR	1,400	6,228	No	
D	Plain Acetal	Carbon Steel	-40	180	NR	-40	82	NR	1,400	6,228	No	
FR	Flame Retardant	Carbon Steel	0	180	NR	-18	82	NR	1,400	6,228	No	
HP™	High Performance	Carbon Steel	-40	180	NR	-40	82	NR	1,400	6,228	No	
HS	Heat Stabilized	Carbon Steel	-40	220	NR	-40	104	NR	1,400	6,228	No	
MR	Melt Resistant	Carbon Steel	-80	220	NR	-62	104	NR	1,400	6,228	No	
WLF	White Low Friction	Carbon Steel	-40	180	NR	-40	82	NR	1,400	6,228	No	
WX	Green Abrasion Resistant Polyamide	Carbon Steel	-40	220	NR	-40	104	NR	1,400	6,228	No	

### Regulatory Information

Rexnord, TableTop and HP are trademarks of Rexnord Industries, LLC. All rights reserved.

### Additional Notes

Stocked in 160 pitch, 10 ft (3.048 m) length strands.  
 Uses 863 carbon steel (S) base chain (Part #863-BC).  
 Chain runs on ANSI No. 60 sprockets.  
 Plain acetal (D) top plates are not stocked for the 3-1/4 in (82.6 mm) width.  
 Chain breakers available.  
 Chain strength is listed at room temperature. NR = Not Recommended.  
 For additional material information, see material portfolio.



