




Photo shows 1863 TAB TableTop® Chain with top plates molded in Black Wear Resistant (BWR) material on Carbon Steel (S) base chain.



Chain Information						
Chain Width		Min. Side-flex Radius		Approximate Weight		
desc	in	mm	in	mm	lbs/ft	kg/m
2 1/4	2.25	57.2	14.00	355.6	1.34	2.00



Available Materials											
Prefix	Top Plate Material	Base Chain Material	Temperature						Chain Strength		FDA Approval
			Fahrenheit			Celsius			lbs	N	
			min	max	dry	wet	min	max			
Standard Materials											
LF	Low Friction	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
Made-to-Order Materials											
AS	Anti-Static	Carbon Steel	0	180	NR	-18	82	NR	1,000	4,448	No
BWR	Black Wear Resistant	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
FR	Flame Retardant	Carbon Steel	0	180	NR	-18	82	NR	1,000	4,448	No
HP™	High Performance	Carbon Steel	-40	180	NR	-40	82	NR	1,000	4,448	No
WX	Green Abrasion Resistant Polyamide	Carbon Steel	-40	220	NR	-40	104	NR	1,000	4,448	No

Regulatory Information


Rexnord, TableTop and HP are trademarks of Rexnord Industries, LLC. All rights reserved.

Additional Notes

Stocked in 160 pitch, 10 ft (3.048 m) length strands.
 Uses 63 carbon steel (S) base chain (Part #63-BC).
 Chain runs on ANSI No. 60 sprockets.
 Chain breakers available.
 For additional material information, see material portfolio.


Corner Track (Two Piece)



Corner track kit supplied as one 90° inside and one 90° outside track, which can be used as either carry or return.

Corner Track Kit Number	Accommodates Top Plate Width		Nominal Corner Radius		Inside Track Radius		Outside Track Radius		Thickness		Width		Material	Color	Approximate Corner Track Kit Weight	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm			lbs	kg
TAB Design																
U18R6	All	All	18.0	457	17.3	439	18.7	475	0.75	19.1	1.5	38	UHMWPE	White	2.63	1.19
U24R6	All	All	24.0	610	23.3	592	24.7	627	0.75	19.1	1.5	38	UHMWPE	White	3.51	1.59

Corner Track (Four Piece)



Corner track kit supplied as two 45° inside and two 45° outside track, which can be used as either carry or return.

Corner Track Kit Number	Accommodates Top Plate Width		Nominal Corner Radius		Inside Track Radius		Outside Track Radius		Thickness		Width		Material	Color	Approximate Corner Track Kit Weight	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm			lbs	kg
TAB Design																
U30R6	All	All	30.0	762	29.3	744	30.7	780	0.75	19.1	1.5	38	UHMWPE	White	4.38	1.99